

Product Datasheet
47448989



47448989

SCHUKO soc.out. hinged cover,enhncd contact prot.,var. in 45°step,S1/B3/7

Technical Features

Electric current	
Rated current	16 A

Voltage	
Rated voltage	250 V
Nominal voltage	250 - 250 V

Frequency	
Frequency	50 - 60 Hz

Materials	
Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions	
Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	35 mm
Built-in depth	32 mm

Connection	
Connector/plug type	Plug clamp

Installation, mounting	
Mounting on	Flush mounting

Connectivity	
Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

Equipment	
Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories	
Has labelling field	No

Cover, door	
Type of lid	Self-closing hinged cover

Capacity	
Number of modules	1

Safety	
With enhanced contact protection	Yes
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

Functions	
With orientation lighting	No
With function lighting	No

Product Datasheet

47448989

Texts	
Imprint	With imprint
Cover	Central cover plate
Type of connection	With plug-in terminals

Suitable for	
S.x/B.x	

Sustainability	
Halogen free	Yes
RoHS conform	Yes