



283510

Extension units insert f. univ. rot. dimmer, soft-lock, 1930/glass, p.white gl.

Technical Features

Voltage

| | |
|-------------------|-------------|
| Operating voltage | 230 - 230 V |
|-------------------|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Materials

| | |
|----------|------------------|
| Colour | Polar white |
| RAL code | 9010 |
| Material | Metal Plastic |

Dimensions

| | |
|---------------|-------|
| Diameter axis | 4 mm |
| Height | 71 mm |
| Width | 71 mm |
| Depth | 61 mm |

Architecture

| | |
|---------------------------|------------------------|
| Control/operation element | Push & rotative switch |
|---------------------------|------------------------|

Texts

| | |
|--------------------|---|
| Voltage | Voltage test possible without dismantling |
| Installation mode | For screw fastening |
| Type of connection | With plug-in terminals |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |