



WFSS82PSW-USBS

**13A 2 Gang Double Pole Switched Socket c/w Twin USB Port Polished Steel White sh**

**Technical Features**

**Electric current**

Rated current	13 A
---------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

**Dimensions**

Height	86 mm
Width	146 mm
Depth	39.10 mm
Built-in depth flush-mounted boxes	25 mm

**Installation, mounting**

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting
Connector/plug type USB	A

**Equipment**

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	0
-------------------	---

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	With imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes