

# Product Datasheet

## WMPS12RB



WMPS12RB

### Push Switch with Bell Symbol

#### Technical Features

<b>Electric current</b>	
Switching current	10 A
Momentary contact current	10 A

<b>Voltage</b>	
Rated voltage	250 V

<b>Architecture</b>	
Number of poles	2

<b>Materials</b>	
Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Coated
Transparent	No

<b>Dimensions</b>	
Height	86 mm
Width	86 mm
Depth	24 mm

<b>Installation, mounting</b>	
Mounting on	Flush mounting

<b>Controls and indicators</b>	
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

<b>Connectivity</b>	
Type of connection	Screw terminal

<b>Safety</b>	
Ingress Protection (IP) class	IP20

<b>Texts</b>	
Imprint	Without imprint
Installation mode	For flush-mounted and hollow wall mounting
Switch mode	NO contact

<b>Sustainability</b>	
REACH-SVHC free	Yes
RoHS conform	Yes