



VF212PF3

Small distributor,golf,flush,2row,24M,IP40,MS-terminal,PE,white door

Technical Features

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Flush mounting

Electric current

Rated current 63 A

Equipment

Number of rails 2

Number of rows 2

Number of section in width 1

With lock No

Has neutral terminal block No

Capacity

Number of modules 24

Functions

Has protection main switch No

With conduit inlets Yes

Scope of delivery

Number of RCCB in enclosure 0

Dimensions

Height 418 mm

Width 382 mm

Depth 97.50 mm

Built-in height 382 mm

Built-in width 318 mm

Cover, door

Number of cabinet doors 1

Dimensions

Built-in depth 72 mm

Cover, door

Number of locks 0

Dimensions

Number of width units 12

Cover, door

Door/cover is transparent No

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Materials

Ultraviolet-resistant No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

Sustainability

RoHS conform	Yes
--------------	-----