

Product Datasheet

JN2B00010S2



JN2B00010S2

250A Panel BOARD 10WAY Surface

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Electric current

| | |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

Equipment

| | |
|--------------------|----|
| Has mounting plate | No |
|--------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Dimensions

| | |
|--------|---------|
| Height | 1000 mm |
| Width | 615 mm |
| Depth | 165 mm |

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 1 |
| Door/cover is transparent | No |

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 9002 |
| Colour | Grey white |

Safety

| | |
|-------------------------------|------------------------------|
| Protection class | Isolation class I |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP41 |
| Locking type | Special tool Without lock |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|