

# Product Datasheet

## FWB73



FWB73

FWB encl.,univers,7rows 252 mod cl.II IP44,plain door,1100x800x161mm,brass term.

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	21
Number of rows	7
Number of section in width	3
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	252
-------------------	-----

#### Functions

Has protection main switch	No
With conduit inlets	Yes

#### Dimensions

Height	1100 mm
Width	800 mm
Depth	165 mm

#### Cover, door

Number of cabinet doors	2
-------------------------	---

#### Dimensions

Built-in depth	161 mm
----------------	--------

#### Cover, door

Number of locks	0
-----------------	---

#### Dimensions

Number of width units	36
-----------------------	----

#### Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

#### Connection

Number of conduit inlets	12
--------------------------	----

#### Connectivity

Mounting type	Surface mounting
---------------	------------------

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK09

# Product Datasheet

## FWB73

---

### Safety

Ingress Protection (IP) class	IP44
Locking type	Bar lock Without lock

### Sustainability

RoHS conform	Yes
--------------	-----