

# Product Datasheet

## VML912C



VML\_SIZE\_6

### 12 Way Conf 100A Switch 2\*100A 30mA RCCB Met

#### Technical Features

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Architecture

Number of poles	2
-----------------	---

##### Functions

Has protection main switch	Yes
----------------------------	-----

##### Capacity

Number of modules	12
-------------------	----

##### Electric current

Rated current	100 A
---------------	-------

##### Dimensions

Depth	100 mm
Height	245 mm
Width	404.20 mm

##### Cover, door

Interlockable	No
Door/cover is transparent	No

##### Materials

RAL code	9010
Colour	Pure white
Material	Steel

##### Connection

Number of accessible phases	2
-----------------------------	---

##### Scope of delivery

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

##### Equipment

Number of rows	1
Number of rails	1

##### Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

##### Sustainability

RoHS conform	Yes
--------------	-----