


Product Datasheet

20307103



20307103



Thermostat, NC contact, centre plate, rocker switch, K.5, al., matt, lacq.

Technical Features

Electric current

Rated current	10 A
Switching current	10 A

Voltage

Nominal voltage	250 - 250 V
Rated voltage	250 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Settings

Comfort temperature setpoint	5 - 30 °C
------------------------------	-----------

Materials

Colour	Aluminium
RAL code	9006
Surface finish	Matt
Material	Metal Plastic
Treatment	Varnished

Dimensions

Height	71 mm
Width	71 mm
Depth	50.90 mm

Screen

With display	No
--------------	----

Equipment

Switching temperature difference	0.50 K
Type of thermostat	Room thermostat
Type of probe	Bimetal

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Type of contacts	1NC
------------------	-----

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint
Junction	With separate connection for night lowering

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes