



KD190B

Insulated busbar 1P 100A fork 20mm² 57M

Technical Features

Electric current	
Rated current	100 A
Architecture	
Number of poles	1
Dimensions	
Length	1000 mm
Voltage	
Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	415 - 415 V
Connection	
Cross-section rigid conductor	20 mm²
Connector/plug type	Phase busbar with fork
Capacity	
Number of modules	57
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes