



VM_SIZE_3

6 Way 63A 30mA Type A RCCB Incomer with Knockouts

Technical Features

Installation, mounting

Mounting on Surface mounting

Architecture

Number of poles 2

Capacity

Number of modules 6

Electric current

Rated current 63 A

Dimensions

Depth 102 mm

Height 240 mm

Width 221 mm

Cover, door

Interlockable No

Door/cover is transparent No

Materials

RAL code 9010

Colour Pure white

Material Steel

Equipment

Number of rows 1

Safety

Ingress Protection (IP) class IP2XC

Sustainability

RoHS conform Yes