
Product Datasheet
WGCXS216UINB



WGCXS216UINB

16A 2+3 PIN UNIVERSAL SOCKET, NB

Technical Features

Voltage	
Rated voltage	250 V
Electric current	
Output current	0 mA
Rated current	16 A
Voltage	
Output voltage	0-0 V
Use conditions	
Operating temperature	-20 - 45 °C
Frequency	
Frequency	50 - 60 Hz
Power	
Output power	0 W
Power consumption standby	0 W
Materials	
Colour	Bronze
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Coated
Contains recycled material (% of total plastic weight)	0 %
Dimensions	
Height	38 mm
Width	86 mm
Depth	29 mm
Cable	
Cable length	0 m
Dimensions	
Built-in depth flush-mounted boxes	35 mm
Built-in depth	29 mm
Connection	
Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm^2
Number of conduit inlets	0
Installation, mounting	
Mounting on	Flush mounting
Mounting-/Connection Position	Back
Connectivity	
Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard
Equipment	
Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Equipment	
With lock	No
Accessories	
Has labelling field	No
Pre-equipped with	None
Capacity	
Number of modules	0
Safety	
With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20
Functions	
With orientation lighting	No
With function lighting	No
Identification	
With imprint	No
Suitable for	
shark	
Sustainability	
REACh-SVHC free	Yes