

# Product Datasheet

## JK116EG



JK116EG

### JK1 16 Module DIN Rail Box Glazed

#### Technical Features

##### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

##### Electric current

|               |       |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

##### Equipment

|                            |     |
|----------------------------|-----|
| Number of rows             | 1   |
| With lock                  | Yes |
| Has neutral terminal block | Yes |

##### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 16 |
|-------------------|----|

##### Dimensions

|        |           |
|--------|-----------|
| Height | 300 mm    |
| Width  | 465 mm    |
| Depth  | 165.50 mm |

##### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

##### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 16 |
|-----------------------|----|

##### Cover, door

|                           |     |
|---------------------------|-----|
| Door/cover is transparent | Yes |
|---------------------------|-----|

##### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

##### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

##### Safety

|                               |                               |
|-------------------------------|-------------------------------|
| Protection class              | Isolation class III           |
| Impact resistance IK          | IK05                          |
| Ingress Protection (IP) class | IP30                          |
| Locking type                  | Key lock<br>Quarter turn lock |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|