



75310002



**Technical Features**

**Settings**

Supported configuration mode ETS

**Connectivity**

With bus system KNX Yes  
With bus system KNX radio No

**Dimensions**

Dimensions 90 x 144 mm  
Height 90 mm  
Width 144 mm  
Depth 70 mm  
Number of width units 8

**Electric current**

Rated current 16 A

**Materials**

Colour Light grey

**Equipment**

Radio frequency bidirectional No

**Frequency**

Frequency 50 - 60 Hz

**Power**

Power incandescent lamp 230 V 3000 - 3000 W

**Voltage**

Rated operational voltage Ue 230 - 230 V  
Operating voltage over bus 21 - 32 V

**Safety**

Ingress Protection (IP) class IP20

**Use conditions**

Operating temperature -5 - 45 °C

**Texts**

Function With positioning function for blind and lamella position  
With safety functions e.g. for wind sensor  
With sun shade function  
Type of connection With screw terminals

**Sustainability**

REACH-SVHC free Yes  
RoHS conform Yes