



75310002



Technical Features

Settings

Supported configuration mode

ETS

Connectivity

With bus system KNX

Yes

With bus system KNX radio

No

Dimensions

Dimensions

90 x 144 mm

Height

90 mm

Width

144 mm

Depth

70 mm

Number of width units

8

Electric current

Rated current

16 A

Materials

Colour

Light grey

Equipment

Radio frequency bidirectional

No

Frequency

Frequency

50 - 60 Hz

Power

Power incandescent lamp 230 V

3000 - 3000 W

Voltage

Rated operational voltage Ue

230 - 230 V

Operating voltage over bus

21 - 32 V

Safety

Ingress Protection (IP) class

IP20

Use conditions

Operating temperature

-5 - 45 °C

Texts

Function

With positioning function for blind and lamella position
With safety functions e.g. for wind sensor
With sun shade function

Type of connection

With screw terminals

Sustainability

REACH-SVHC free

Yes

RoHS conform

Yes