



WBMSF3-MB

**Mech 75VA 3 speed fan cont c/w capacitor MB**

**Technical Features**

**Voltage**

Nominal voltage	250 - 250 V
-----------------	-------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Electric current**

Rated current	10 A
---------------	------

**Dimensions**

Dimensions	27 x 27 mm
Built-in depth flush-mounted boxes	46 mm

**Materials**

Colour	Black
Treatment	Varnished

**Architecture**

Control/operation element	Rotative
---------------------------	----------

**Connection**

Connector/plug type	RotoLoc®
---------------------	----------

**Texts**

Switch mode	With neutral position "OFF": OFF-1-2-3
Type of connection	With screw terminals

**Sustainability**

RoHS conform	Yes
--------------	-----