

Product Datasheet

WBMSF3-MW



WBMSF3-MW

Mech 75VA 3 speed fan cont c/w cap MW

Technical Features

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Dimensions	27 x 27 mm
Built-in depth flush-mounted boxes	46 mm

Materials

Colour	White
Treatment	Varnished

Architecture

Control/operation element	Rotative
---------------------------	----------

Texts

Switch mode	With neutral position "OFF": OFF-1-2-3
Type of connection	With screw terminals

Sustainability

RoHS conform	Yes
--------------	-----