



WBMSF3-MW

**Mech 75VA 3 speed fan cont c/w cap MW**

**Technical Features**

**Voltage**

Nominal voltage 250 - 250 V

**Installation, mounting**

Mounting on Flush mounting

**Safety**

Ingress Protection (IP) class IP20

**Electric current**

Rated current 10 A

**Dimensions**

Dimensions 27 x 27 mm

Built-in depth flush-mounted boxes 46 mm

**Materials**

Colour White

Treatment Varnished

**Architecture**

Control/operation element Rotative

**Connection**

Connector/plug type RotoLoc®

**Texts**

Switch mode With neutral position "OFF": OFF-1-2-3

Type of connection With screw terminals

**Sustainability**

RoHS conform Yes