

# Product Datasheet

## WBMSF3-MW



WBMSF3-MW

### Mech 75VA 3 speed fan cont c/w cap MW

#### Technical Features

##### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 250 - 250 V |
|-----------------|-------------|

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Dimensions

|                                    |            |
|------------------------------------|------------|
| Dimensions                         | 27 x 27 mm |
| Built-in depth flush-mounted boxes | 46 mm      |

##### Materials

|           |           |
|-----------|-----------|
| Colour    | White     |
| Treatment | Varnished |

##### Architecture

|                           |          |
|---------------------------|----------|
| Control/operation element | Rotative |
|---------------------------|----------|

##### Texts

|                    |                                        |
|--------------------|----------------------------------------|
| Switch mode        | With neutral position "OFF": OFF-1-2-3 |
| Type of connection | With screw terminals                   |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|