



WBMSF3-MW

Mech 75VA 3 speed fan cont c/w cap MW

Technical Features

Voltage

Nominal voltage 250 - 250 V

Installation, mounting

Mounting on Flush mounting

Safety

Ingress Protection (IP) class IP20

Electric current

Rated current 10 A

Dimensions

Dimensions 27 x 27 mm

Built-in depth flush-mounted boxes 46 mm

Materials

Colour White

Treatment Varnished

Architecture

Control/operation element Rotative

Connection

Connector/plug type RotoLoc®

Texts

Switch mode With neutral position "OFF": OFF-1-2-3

Type of connection With screw terminals

Sustainability

RoHS conform Yes