



WMPS3PIFL

3 Pole Isolator Switch Lockable with Fan Symbol

Technical Features

Electric current

Switching current 10 A

Installation, mounting

Mounting on Flush mounting
Surface mounting

Voltage

Rated voltage 250 V

Materials

Colour White
Surface finish Glossy
Material Urea formaldehyde
Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm
Built-in depth 13.10 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Texts

Lighting Without lighting (cannot be illuminated)
Switch mode 3-pole

Sustainability

REACH-SVHC free Yes
RoHS conform Yes