



85421101

**Universal Push button Dimmer 1gang (R,L, C, LED), Round supporting ring**

**Technical Features**

**Voltage**

Operating voltage	230 - 230 V
-------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Material	Metal Plastic
----------	------------------

**Dimensions**

Built-in depth	32 mm
Height	71 mm
Width	71 mm
Depth	33.20 mm

**Architecture**

Control/operation element	Single push button
---------------------------	--------------------

**Power**

Power consumption standby	0.30 W
---------------------------	--------

**Lighting**

Dimmable 230 V LED lamp	3 - 120 W
LED lamp power	250 W

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Capacity**

Number of modules	0
-------------------	---

**Texts**

Dimming principle	Automatic setting of load-dependent switching principle (autodetect process)
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals
Extension unit input	Without 230 V extension unit inputs
Operation and control	No Bluetooth interface

**Sustainability**

RoHS conform	Yes
--------------	-----