

# Product Datasheet

## WNE123B



WNE123B

### cubyko Triple horizontal socket 2P+E screwless flush mounted white IP55

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

##### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Pure white
RAL code	9010
Surface finish	Matt Satin finish
Material	Polypropylene (PP)

##### Dimensions

Height	45 mm
Width	135 mm
Depth	42.50 mm
Built-in depth flush-mounted boxes	40 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	French norm NF
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	Yes
With signal lamp	No

##### Cover, door

Type of lid	Self-closing hinged cover, can be arrested in end position
-------------	--

##### Capacity

Number of modules	6
-------------------	---

##### Safety

With enhanced contact protection	No
Impact resistance IK	IK07
Ingress Protection (IP) class	IP55

##### Functions

With orientation lighting	No
---------------------------	----

##### Texts

Imprint	With imprint
Cover	For covering of socket outlets
Protection	Without protective screen

##### Suitable for

Hager cubyko	
--------------	--