

Enclosed MCCB 4-Pole 250A, 25kA (Adjustable 160A -200A - 250A)

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Overvoltage protection	Yes
------------------------	-----

Electric current

Rated current	250 A
---------------	-------

Dimensions

Depth	135 mm
Height	660 mm
Width	260 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	7035
Colour	Light grey
Material	Steel

Connection

Number of accessible phases	3
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

Equipment

With socket outlet	No
--------------------	----

Safety

Ingress Protection (IP) class	IP3X
Protection class	Isolation class III

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes