



VS108TM

Small distributor,golf,surface,1row,IP40,8M,MS-terminal,N+PE,transparent door

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	8
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	184 mm
Width	210 mm
Depth	99 mm

Cover, door

Number of cabinet doors	1
Number of locks	0

Dimensions

Number of width units	8
-----------------------	---

Cover, door

Door/cover is transparent	Yes
Cabinet door type	Single door

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials

Ultraviolet-resistant	No
-----------------------	----

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Locking type	Snap on lock Without lock
Glow wire test	650 °C
Protection class with door	IP40

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes
