


Product Datasheet

503808



503808



Series push-button 2 change-over contacts with isolated input terminals

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Double rocker
---------------------------	---------------

Materials

Material	Metal Plastic
Treatment	Untreated
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	41.60 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	2
Type of push button	Series push button
With feedback signal contact	No

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Texts

Imprint	Without imprint
Installation mode	With spreader claws
Lighting	For illumination
Switch mode	Double change-over contact, usable as NC or NO with separate input terminals
Type of connection	With screw terminals

Suitable for

K.x / Q.x / R.x / S.x/B.x

Sustainability

RoHS conform	Yes
--------------	-----