


Product Datasheet

TYA604B



TYA604B



Output module 4x 10A /230V~, KNX

Technical Features

Settings

Supported configuration mode	ETS
------------------------------	-----

Connectivity

With bus system KNX	Yes
With bus system KNX radio	No

Dimensions

Dimensions	90 x 70 mm
Height	90 mm
Width	70 mm
Number of width units	4

Electric current

Rated current	10 A
---------------	------

Materials

Colour	Light grey
--------	------------

Equipment

Radio frequency bidirectional	No
With switch for manual switch	Yes

Electric current

Bus current consumption while idle	3 mA
------------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Power incandescent lamp 230 V	1200 - 1200 W
Output power	1200 W
230 V incandescent and halogen lamp	1200 W

Voltage

Rated operational voltage Ue	230 - 230 V
System supply voltage	30 V DC Via bus
Operating voltage over bus	21 - 32 V

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section rigid conductor	0.75 - 2.5 mm ²
Cross-section flexible conductor	0.75 - 2.5 mm ²

Texts

Function	With safety functions e.g. for wind, rain, alarm With positioning function for blind and lamella position With sun shade function
Type of connection	With quickconnect plug-in terminals

Sustainability

RoHS conform	Yes
--------------	-----