



VT18S

**18M 1Row DIN Surface Metal BOX, No Door**

**Technical Features**

**Voltage**

Nominal voltage	230 - 415 V
-----------------	-------------

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Equipment**

Number of rails	1
Number of rows	1

**Capacity**

Number of modules	18
-------------------	----

**Dimensions**

Height	259 mm
Width	417 mm
Depth	71 mm
Built-in depth	70 mm

**Cover, door**

Number of locks	0
-----------------	---

**Dimensions**

Number of width units	18
-----------------------	----

**Cover, door**

Door/cover is transparent	No
---------------------------	----

**Connection**

Number of conduit inlets	16
--------------------------	----

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Materials**

Material	Steel
RAL code	9002
Colour	Grey white

**Equipment**

Has mounting plate	No
--------------------	----

**Safety**

Protection class	Isolation class I
Impact resistance IK	IK05

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes