



WGCXHDCEG

### 16AX DND&MUR SWITCH W/ LED (INDOOR), EG

#### Technical Features

##### Electric current

Switching current	16 A
-------------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Gold
--------	------

Surface finish	Matt
----------------	------

Treatment	Varnished
-----------	-----------

#### Controls and indicators

Number of buttons	2
-------------------	---

#### Dimensions

Dimensions	86 x 86 mm
------------	------------

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Double push button
---------------------------	--------------------

##### Electric current

Rated current	16 A
---------------	------

#### Texts

Switch mode	2-way
-------------	-------

#### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----