



WG CXHDCEG

**16AX DND&MUR SWITCH W/ LED (INDOOR), EG**

**Technical Features**

**Electric current**

Switching current 16 A

**Voltage**

Rated voltage 250 V

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Gold

Surface finish Matt

Treatment Varnished

**Controls and indicators**

Number of buttons 2

**Dimensions**

Dimensions 86 x 86 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Double push button

**Electric current**

Rated current 16 A

**Texts**

Switch mode 2-way

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes