



TYA608B



Output module 8x 10A /230V~, KNX

Technical Features

Settings

Supported configuration mode

ETS

Connectivity

With bus system KNX

Yes

With bus system KNX radio

No

Dimensions

Dimensions

90 x 105 mm

Height

90 mm

Width

105 mm

Number of width units

6

Electric current

Rated current

10 A

Materials

Colour

Light grey

Equipment

Radio frequency bidirectional

No

With switch for manual switch

Yes

Electric current

Bus current consumption while idle

9 mA

Frequency

Frequency

50 - 60 Hz

Power

Power incandescent lamp 230 V

1200 - 1200 W

Output power

1200 W

230 V incandescent and halogen lamp

1200 W

Voltage

Rated operational voltage Ue

230 - 230 V

System supply voltage

30 V DC Via bus

Operating voltage over bus

21 - 32 V

Safety

Ingress Protection (IP) class

IP20

Use conditions

Operating temperature

-5 - 45 °C

Connection

Cross-section rigid conductor

0.75 - 2.5 mm²

Cross-section flexible conductor

0.75 - 2.5 mm²

Texts

Function

With safety functions e.g. for wind, rain, alarm
With positioning function for blind and lamella position
With sun shade function

Type of connection

With quickconnect plug-in terminals

Sustainability

RoHS conform

Yes