



BC225N

Earth leakage add-on block 2P 25A 10mA A Class

Technical Features

Voltage

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current Idn	10 mA
Rated current	25 A

Architecture

Number of poles	2
Neutral position	Right

Capacity

Number of modules	2
-------------------	---

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	70 mm
Width	35 mm
Depth	92 mm