



503511

Series push-button, light control

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Double rocker
---------------------------	---------------

Materials

Treatment	Untreated
Transparent	No

Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth flush-mounted boxes	35 mm

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Controls and indicators

Number of buttons	2
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

Accessories

Has labelling field	No
---------------------	----

Suitable for

Serie 1930 / Serie Glas / Serie R.classic

Sustainability

Halogen free	Yes
RoHS conform	Yes