

# Product Datasheet

## WGCXHDCKB



WGCXHDCKB

### 16AX DND&MUR SWITCH W/ LED (INDOOR), KB

#### Technical Features

|                         |      |
|-------------------------|------|
| <b>Electric current</b> |      |
| Switching current       | 16 A |

|                |       |
|----------------|-------|
| <b>Voltage</b> |       |
| Rated voltage  | 250 V |

|                  |            |
|------------------|------------|
| <b>Frequency</b> |            |
| Frequency        | 50 - 60 Hz |

|                  |              |
|------------------|--------------|
| <b>Materials</b> |              |
| Colour           | Knight black |
| Surface finish   | Matt         |
| Treatment        | Varnished    |

|                                |   |
|--------------------------------|---|
| <b>Controls and indicators</b> |   |
| Number of buttons              | 2 |

|                   |            |
|-------------------|------------|
| <b>Dimensions</b> |            |
| Dimensions        | 86 x 86 mm |

|                               |      |
|-------------------------------|------|
| <b>Safety</b>                 |      |
| Ingress Protection (IP) class | IP20 |

|                           |                    |
|---------------------------|--------------------|
| <b>Architecture</b>       |                    |
| Control/operation element | Double push button |

|                         |      |
|-------------------------|------|
| <b>Electric current</b> |      |
| Rated current           | 16 A |

|              |       |
|--------------|-------|
| <b>Texts</b> |       |
| Switch mode  | 2-way |

|                       |     |
|-----------------------|-----|
| <b>Sustainability</b> |     |
| REACH-SVHC free       | Yes |
| RoHS conform          | Yes |