

# Product Datasheet

## WGCXHDCKB



WGCXHDCKB

### 16AX DND&MUR SWITCH W/ LED (INDOOR), KB

#### Technical Features

Electric current	
Switching current	16 A

Voltage	
Rated voltage	250 V

Frequency	
Frequency	50 - 60 Hz

Materials	
Colour	Knight black
Surface finish	Matt
Treatment	Varnished

Controls and indicators	
Number of buttons	2

Dimensions	
Dimensions	86 x 86 mm

Safety	
Ingress Protection (IP) class	IP20

Architecture	
Control/operation element	Double push button

Electric current	
Rated current	16 A

Texts	
Switch mode	2-way

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes