



WG CXHDCKB

16AX DND&MUR SWITCH W/ LED (INDOOR), KB

Technical Features

Electric current

Switching current 16 A

Voltage

Rated voltage 250 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour Knight black

Surface finish Matt

Treatment Varnished

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 86 x 86 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Double push button

Electric current

Rated current 16 A

Texts

Switch mode 2-way

Sustainability

REACH-SVHC free Yes

RoHS conform Yes