



VZ025D

Pressure balance screw joint, vector, IP66, M25

Technical Features

Dimensions

Spanner width in mm	32 mm
Thread length	8 mm

Connection

Clamping range	9 - 17 mm
----------------	-----------

Materials

Material	Plastic Thermoplastic
Colour	Light grey
RAL code	7035
Treatment	Untreated

Safety

Impact-resistant	Yes
Ingress Protection (IP) class	IP65

Use conditions

Operating temperature	-25 - 40 °C
-----------------------	-------------

Equipment

Thread size metric	0 - 25
With bending protection	Yes
With locknut	Yes
Safe use in explosive atmosphere	No
Thread pitch	1.50

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes