



VZ020D

Pressure balance screw joint,vector,IP66, M20

Technical Features

Dimensions

| | |
|---------------------|-------|
| Spanner width in mm | 27 mm |
| Thread length | 8 mm |

Connection

| | |
|----------------|-----------|
| Clamping range | 6 - 13 mm |
|----------------|-----------|

Materials

| | |
|-----------|--------------------------|
| Material | Plastic Thermoplastic |
| Colour | Light grey |
| RAL code | 7035 |
| Treatment | Untreated |

Safety

| | |
|-------------------------------|------|
| Impact-resistant | Yes |
| Ingress Protection (IP) class | IP65 |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -25 - 40 °C |
|-----------------------|-------------|

Equipment

| | |
|----------------------------------|--------|
| Thread size metric | 0 - 20 |
| With bending protection | Yes |
| With locknut | Yes |
| Safe use in explosive atmosphere | No |
| Thread pitch | 1.50 |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |