



VZ020D

**Pressure balance screw joint,vector,IP66, M20**

**Technical Features**

**Dimensions**

Spanner width in mm	27 mm
Thread length	8 mm

**Connection**

Clamping range	6 - 13 mm
----------------	-----------

**Materials**

Material	Plastic Thermoplastic
Colour	Light grey
RAL code	7035
Treatment	Untreated

**Safety**

Impact-resistant	Yes
Ingress Protection (IP) class	IP65

**Use conditions**

Operating temperature	-25 - 40 °C
-----------------------	-------------

**Equipment**

Thread size metric	0 - 20
With bending protection	Yes
With locknut	Yes
Safe use in explosive atmosphere	No
Thread pitch	1.50

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes