Product Datasheet
VZ020D



VZ020D

Pressure balance screw joint,vector,IP66, M20

Technical Features

Dimensions

Spanner width in mm	27 mm
Thread length	8 mm

Connection

Clamping range	6 - 13 mm

Materials

Material	Plastic Thermoplastic
Colour	Light grey
RAL code	7035
Treatment	Untreated

Safety

Impact-resistant	Yes
Ingress Protection (IP) class	IP65

Use conditions

Operating temperature	-25 - 40 °C

Equipment

Thread size metric	0 - 20
With bending protection	Yes
With locknut	Yes
Safe use in explosive atmosphere	No
Thread pitch	1.50

Sustainability

REACh-SVHC free	Yes
RoHS conform	Yes