



WGCXHDCNB

#### 16AX DND&MUR SWITCH W/ LED (INDOOR), NB

##### Technical Features

###### Electric current

Switching current	16 A
-------------------	------

###### Voltage

Rated voltage	250 V
---------------	-------

###### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Bronze
--------	--------

Surface finish	Matt
----------------	------

Treatment	Varnished
-----------	-----------

##### Controls and indicators

Number of buttons	2
-------------------	---

##### Dimensions

Dimensions	86 x 86 mm
------------	------------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Double push button
---------------------------	--------------------

###### Electric current

Rated current	16 A
---------------	------

##### Texts

Switch mode	2-way
-------------	-------

##### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----