



47438903

**SCHUKO soc. out. "SV" imprint, S.1/B.3/B.7, green glossy**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Green  
RAL code 6029  
Surface finish Glossy  
Material Duroplastic  
Treatment Untreated

**Dimensions**

Height 71 mm  
Width 71 mm  
Number of units 1  
Built-in depth flush-mounted boxes 31 mm  
Built-in depth 32 mm

**Connection**

Connector/plug type Plug-in terminal

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Plug-in connection  
Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO  
Rotated central insert No  
With hinged lid No  
With round protective earth pin No  
With signal lamp No  
With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection No  
Impact resistance IK IK02  
Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No  
With function lighting No

**Texts**

Imprint With imprint "SV"  
Cover Central cover plate

---

**Texts**

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

---

**Suitable for**

S.x/B.x

---

**Sustainability**

Halogen free	Yes
RoHS conform	Yes