



VZ016M

Cable gland, vector, IP65, M16, plastic

Technical Features

Dimensions

Height	35.50 mm
Spanner width in mm	20 mm
Thread length	8 mm

Connection

Clamping range	5 - 10 mm
----------------	-----------

Materials

Material	Polyamide (PA) Thermoplastic
Colour	Light grey
RAL code	7035
Treatment	Untreated

Safety

Impact-resistant	Yes
Ingress Protection (IP) class	IP65

Use conditions

Operating temperature	-20 - 100 °C
-----------------------	--------------

Equipment

Thread size metric	0 - 16
With bending protection	Yes
With locknut	Yes
Safe use in explosive atmosphere	No
Thread pitch	1.50

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes