

Enclosed Non-Auto MCCB 4-Pole, 250A, 25kA

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Functions**

Overvoltage protection Yes

**Electric current**

Rated current 250 A

**Dimensions**

Depth 135 mm

Height 660 mm

Width 260 mm

**Cover, door**

Interlockable No

Door/cover is transparent No

**Materials**

RAL code 7035

Colour Light grey

Material Steel

**Connection**

Number of accessible phases 3

**Scope of delivery**

Number of RCCB in enclosure 0

**Equipment**

With socket outlet No

**Safety**

Ingress Protection (IP) class IP3X

Protection class Isolation class III

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes