

Product Datasheet

SU214



SU214

Buzzer 12V

Technical Features

Electric current

| | |
|---------------|--------|
| Rated current | 0.33 A |
|---------------|--------|

Dimensions

| | |
|------------|------------|
| Dimensions | 80 x 18 mm |
| Height | 80 mm |
| Width | 18 mm |
| Depth | 65 mm |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -10 - 40 °C |
| Storage/transport temperature | -25 - 60 °C |

Connection

| | |
|----------------------------------|-------------------|
| Cross-section flexible conductor | 4 mm ² |
| Cross-section rigid conductor | 6 mm ² |

Power

| | |
|---------------------------|------|
| Total power loss under IN | 4 W |
| Power consumption VA | 4 VA |

Equipment

| | |
|-------------|----|
| Noise level | 78 |
|-------------|----|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Voltage

| | |
|------------------------------|----------|
| Rated operational voltage Ue | 8 - 12 V |
|------------------------------|----------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

Illustrations | Drawings

