



SU214

**Buzzer 12V**

**Technical Features**

**Electric current**

|               |        |
|---------------|--------|
| Rated current | 0.33 A |
|---------------|--------|

**Dimensions**

|            |            |
|------------|------------|
| Dimensions | 80 x 18 mm |
| Height     | 80 mm      |
| Width      | 18 mm      |
| Depth      | 65 mm      |

**Use conditions**

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -10 - 40 °C |
| Storage/transport temperature | -25 - 60 °C |

**Connection**

|                                  |                   |
|----------------------------------|-------------------|
| Cross-section flexible conductor | 4 mm <sup>2</sup> |
| Cross-section rigid conductor    | 6 mm <sup>2</sup> |

**Power**

|                           |      |
|---------------------------|------|
| Total power loss under IN | 4 W  |
| Power consumption VA      | 4 VA |

**Equipment**

|             |    |
|-------------|----|
| Noise level | 78 |
|-------------|----|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Voltage**

|                              |          |
|------------------------------|----------|
| Rated operational voltage Ue | 8 - 12 V |
|------------------------------|----------|

**Illustrations | Drawings**

