



SU215

## Buzzer 230V

### Technical Features

#### Electric current

Rated current	0.03 A
---------------	--------

#### Dimensions

Dimensions	80 x 18 mm
Height	80 mm
Width	18 mm
Depth	65 mm

#### Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

#### Connection

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

#### Power

Total power loss under IN	6.50 W
Power consumption VA	6.50 VA

#### Equipment

Noise level	78
-------------	----

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Capacity

Number of modules	1
-------------------	---

#### Voltage

Rated operational voltage U <sub>e</sub>	230 - 230 V
--	-------------

### Illustrations | Drawings

