



SU213

Bell 230V

Technical Features

Capacity

Number of modules	1
-------------------	---

Connection

Cross-section flexible conductor	4 mm ²
Cross-section rigid conductor	6 mm ²

Dimensions

Depth	65 mm
Dimensions	80 x 18 mm
Height	80 mm
Width	18 mm

Electric current

Rated current	0.03 A
---------------	--------

Equipment

Noise level	85
-------------	----

Frequency

Frequency	0 - 50 Hz
-----------	-----------

Power

Power consumption VA	6.50 VA
Total power loss under IN	6.50 W

Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Illustrations | Drawings

