

# Product Datasheet

## SU213



SU213

### Bell 230V

#### Technical Features

##### Electric current

Rated current	0.03 A
---------------	--------

##### Dimensions

Dimensions	80 x 18 mm
Height	80 mm
Width	18 mm
Depth	65 mm

##### Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

##### Connection

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

##### Power

Total power loss under I <sub>N</sub>	6.50 W
Power consumption VA	6.50 VA

##### Equipment

Noise level	85
-------------	----

##### Frequency

Frequency	0 - 50 Hz
-----------	-----------

##### Capacity

Number of modules	1
-------------------	---

##### Voltage

Rated operational voltage U <sub>e</sub>	230 - 230 V
--	-------------

#### Illustrations | Drawings

