

# Product Datasheet

## SU212



SU212

### Bell 12V

#### Technical Features

##### Electric current

Rated current	0.33 A
---------------	--------

##### Dimensions

Dimensions	80 x 18 mm
Height	80 mm
Width	18 mm
Depth	65 mm

##### Use conditions

Operating temperature	-10 - 40 °C
Storage/transport temperature	-25 - 60 °C

##### Connection

Cross-section flexible conductor	4 mm <sup>2</sup>
Cross-section rigid conductor	6 mm <sup>2</sup>

##### Power

Total power loss under IN	5 W
Power consumption VA	5 VA

##### Equipment

Noise level	85
-------------	----

##### Frequency

Frequency	0 - 50 Hz
-----------	-----------

##### Capacity

Number of modules	1
-------------------	---

##### Voltage

Rated operational voltage Ue	8 - 12 V
------------------------------	----------

##### Sustainability

REACH-SVHC free	Yes
-----------------	-----

#### Illustrations | Drawings

